



Vape Tank Compatibility Guide

VapeGuard Standard 19-28 mm and Large 27-38 mm

STANDARD	LARGE	FINAL FIT CHECK
19-28 mm	27-38 mm	Measure fitted glass
100 model references	100 model references	At the widest outside diameter

Important: These model names are research references, not guaranteed fits. Tank editions, replacement glass, straight glass and bubble glass may have different outside diameters. Always measure the glass actually fitted to your tank. The two VapeGuard ranges overlap at 27-28 mm.

[Search the live compatibility guide](#) | [How to measure vape tank glass](#) | [Choose a VapeGuard](#)

Prepared by VapeGuard Limited | Updated 11 September 2026

Standard 19-28 mm compatibility table

Click any model name to open the live VapeGuard compatibility search. Measure the fitted glass before ordering; model references alone cannot confirm the final fit.

Brand	Tank models to check
Aspire	Nautilus Nautilus 2 Nautilus 3 Nautilus GT Cleito Atlantis Triton Triton 2
Geekvape	Cerberus Z Nano Aero
Innokin	Zenith Zenith II Zenith Pro Zlide Zlide Top
SMOK	TFV8 Baby Beast TFV8 Big Baby Baby V2 TFV12 Prince
Vaporesso	NRG GTX Tank Cascade Baby iTank
Uwell	Crown Crown III Crown IV
Freemax	Fireluke Fireluke 2 Fireluke 3
Eleaf	Melo III Melo 4
KangerTech	Subtank Mini TopTank Mini
Joyetech	Cubis Cubis Pro Cubis Max ProCore Aries ProCore Motor ProCore Air Unimax 22 Ornate Ultimo Exceed D22
Wismec	GNOME GNOME King Amor Amor Mini Amor Plus Elabo Elabo Mini Reux Mini
Sense	Herakles Herakles Plus Herakles 3 Blazer Blazer Mini Screen Cyclone
OBS	Engine Engine Nano Engine II Crius Crius II Cube Tank
Vandy Vape	Kylin Mini Kylin Mini V2 Berserker MTL Berserker Mini Revolver RTA Govad RTA Mesh 24 RTA
Wotofo	Profile Unity Profile M Serpent Mini Serpent SMM Bravo RTA Flow Tank Conqueror Mini

Brand	Tank models to check
OXVA	Arbiter Solo Arbiter 2 Unicoil Tank Origin X RBA Tank Velocity LE Tank Xlim C Tank
Lost Vape	Ultra Boost Tank UB Pro Pod Tank Centaurus Sub-Ohm Tank Gemini Hybrid Ursa Mini Tank
Vapefly	Brunhilde MTL Brunhilde SBS Tank Kriemhild Kriemhild II Nicolas II
Augvape	Intake MTL Intake RTA Merlin Mini Merlin MTL Skynet Sub-Ohm Tank

How to use this table

1. Find the tank model as a starting reference. 2. Confirm the exact tank edition and fitted glass shape. 3. Measure across the widest outside point of that fitted glass. 4. Compare the measurement with the VapeGuard size range.

Large 27-38 mm compatibility table

Click any model name to open the live VapeGuard compatibility search. Measure the fitted glass before ordering; model references alone cannot confirm the final fit.

Brand	Tank models to check
Geekvape	Z (Zeus) Sub-Ohm Z Sub-Ohm 2021 Z Fli Z Max P Sub-Ohm
SMOK	TFV16 TFV18 TFV18 Mini TF Tank
Vaporesso	iTank 2 SKRR NRG-S Cascade
Uwell	Crown V Valyrian Valyrian II Valyrian III
HorizonTech	Falcon Falcon King Falcon 2 Falcon Legend
Freemax	M Pro Mesh Pro Fireluke Solo
VOOPOO	UFORCE UFORCE-L UFORCE-X MAAT
Hellvape	Fat Rabbit Hellbeast Dead Rabbit Tank
Steam Crave	Aromamizer Supreme Aromamizer Plus Aromamizer Ragnar
Dovpo	Blotto Blotto Mini Blotto Max Blotto Single Coil Abyss Bridge Tank College DNA Tank Riva Tank
Vandy Vape	Kylin Kylin V2 Kylin M Kylin M Pro Kylin V3 Pyro RDTA Triple II RDTA
Wotofo	Profile X Profile RDTA Profile PS Dual Mesh Troll X Gear V2 NexMesh Pro Tank Turbo RDTA
OXVA	Arbiter Arbiter 3 Arbiter 3 RDTA Blaze RDTA Blaze Solo RDTA Origin X RDTA
Lost Vape	Centaurus Tank Centaurus Sub Coo UB Max Tank Ursa Quest Multi Tank Gemini RDTA Corrin RDTA
Vapefly	Brunhilde Top Coiler Brunhilde 1o3 Brunhilde 1o3 Extreme Gunther Gunther 2 Siegfried Mesh RDTA

Brand	Tank models to check
Augvape	Intake Dual Druga RTA Merlin Merlin Nano Boreas V2 Zeus X Collaboration Tank
Smoant	Ladon Tank Battlestar Tank Kaiser Tank Talos Tank Pasito RBA Tank
IJOY	Captain Sub-Ohm Captain X3 Diamond Tank Katana Tank Limitless XL Tornado 150
Sense	Herakles V2 Herakles Honor Blazer 200 V-Jet V-Jet Plus
Wismec	Reux Reux Advanced GNOME WM Column Tank Kestrel Tank

How to use this table

1. Find the tank model as a starting reference. 2. Confirm the exact tank edition and fitted glass shape. 3. Measure across the widest outside point of that fitted glass. 4. Compare the measurement with the VapeGuard size range.